


REA VERIFIER

QUALITY CONTROL DEVICES
FOR MATRIX- AND BARCODES

REA VeriCube UV

Quality Control Device
for 2D Matrix- and Barcodes



REA VeriCube UV

The REA VeriCube UV (ultraviolet) is a state-of-the-art matrix and barcode verification device which can be used across all industry sectors. Whether lying, standing or from top to bottom, virtually any test sample can be measured contact-free in the optimum measuring position.

The measurement of optical codes in compliance with defined angles, distances and lighting allows accurate and reproducible measurement results and quality evaluations.


The measuring system is based on a high-precision optical module with a CMOS camera chip. The system is designed to avoid ambient light influences during the measurement process.

The measured values are transmitted via a standard network interface to a PC with REA TransWin32 evaluation software installed.

The verification system consists of the measuring head, an optical module with a wide measuring range to choose from and the Windows based PC evaluation software REA TransWin32.

With the REA Verifier VeriCube you can quickly find out how to improve the read rate of the tested codes.

Optimize the print quality of your codes by utilizing detailed measurement results.



Features

- **Ultraviolet illumination**
- Contact-free measurements by a CMOS camera
- Easy exchangeable camera modules to adapt to different code sizes and measuring distances
- Selectable illumination (red or ultraviolet)
- Designed to operate in 3 positions to meet different measuring requirements: sidewise, in upright position and upside down
- Darkened measuring chamber to avoid ambient light influences
- Verification according to ISO/IEC 15415 for printed matrix codes
- Verification according to ISO/IEC TR 29158 (formerly AIM DPM guideline 2006) for direct part marking matrix codes
- Verification in compliance with GS1 specifications
- Verification of GS1 128 data structures
- Verification of optional parameters for optimizing the print process
- Multilingual user interface and reports
- For ease of use, settings can be stored in customized profiles for fast selection
- ISO/IEC 15418 / ANS MH10.8.2 data structure analysis
- Specific code selection to meet the pharmaceutical industry demands
- Power supply via network cable (Power over Ethernet)
- Easy removable and exchangeable transparent cover plate
- Network-compatible PC evaluation software TransWin32 for Windows (multi user capable)

Code Types

Matrix Codes (2D):

Data Matrix, DPM-Matrix Codes, QR-Code, Micro QR-Code, Aztec Code, PDF 417, HanXin Code, more under development

Barcodes (1D):

EAN-13, UPC-A, UPC-E with/ without Add-On, EAN-8, 2/5 Interleaved, ITF-14, Frachtpost, Code 39, PZN-Code, Code 32, Code 128, GS1 Databar, GS1 Databar Composite

Optional Codes:

2/5 3 Bars, 2/5 5 Bars, 2/5 IATA, 2/5 Baggage, 2/5 DHL Express (Frachtpost-Code), Code 39 Full ASCII, Code 93, MSI, Plessey, Codabar Monarch (18), LAETUS Pharmacode, LAETUS Mini Pharma Code

Options:

REA VeriCube stand, optional Symbologies, ScanLink, Article Look up Software, Data Analysis

Data structures and properties:

- GS1 data structures (GS1 Data Matrix, GS1 QR-Code, GS1-128, GS1 Databar, Composite)
- ISO/IEC 15418 / ANS MH10.8.2 data structures (AIAG, Odette, VDA, EDIFICE, HIBC, DOD, UPU...)
- EFPIA and PPN support for pharmaceutical industry
- Check digit control settings
- Size control settings
- Customizable date verification

The REA VeriCube UV shall be used under protected conditions only. Due to UV Light risk operation under is only allowed in a closed environment accessible for trained staff only.

Technical Data

Fokuslage 0						
Focal length	Field Of View (FOV)	Typical X-dimension		Minimum X-dimension		Pixel size
8 mm	114 x 71 mm	0.46 mm	18 mil	0.25 mm	10 mil	44 µm
12 mm	80 x 60 mm	0.31 mm	12 mil	0.18 mm	7 mil	31 µm
16 mm	64 x 47 mm	0.25 mm	10 mil	0.15 mm	6 mil	25 µm
25 mm	37 x 27 mm	0.15 mm	6 mil	0.09 mm	4 mil	14.5 µm
50 mm	9 x 6 mm	0.042 mm	2 mil	0.036 mm	1 mil	3.6 µm

Each focal length is available with a focal distance adjustment either on the device top plane or with a distance of 15 mm to the device top plane. The 15 mm distance is required for using the REA VeriCube in the stand for measuring of complex 3D parts.

- Measuring accuracy compliant to ISO/IEC 15426-2 and ISO/IEC 15426-1
- Windows Software TransWin32 included
- Ultraviolet light 850 nm or Red LED light 660 nm
- alternative Infrared 940 nm or Red light 940 nm
- Illumination angle 45°, red or ultraviolet
- Status LEDs for scan and light source selection
- Power supply via PoE (Power over Ethernet)
- Key panel with on/off, Scan and 3 customizable-function keys
- Flip key panel to accommodate to preferred measuring position
- RJ45 Ethernet port for TCP/IP communication and PoE Power supply
- Exchangeable camera module, resolution 2592 x 1944 pixel
- Camera focus and aperture pre-adjusted by factory
- Size: 200 x 150 x 150 mm (w/l/h), with key panel 210 mm width
- Weight: 2.600 g
- Windows 7, 8 and 10, 64 bit support



Specifications and features explained here are subject to change without notice

REA VERIFIER



REA Elektronik GmbH

Teichwiesenstrasse 1

64367 Muehlthal

Germany

T: +49 (0)6154 638-0

F: +49 (0)6154 638-195

E: info@rea-verifier.de

www.rea-verifier.com